



Ratcheting Cable Cutter For ACSR up to 556 Max And Aluminum Or Copper Up To 750 kcmil Max

By: CHANCE Lineman Tools & Equipment
Catalog # [C4032980](#)



RATCHETING WIRE CUTTER - 556 ACSR

Features

- Max opening 2", 18" long, 4 lbs 6 oz
- Patented conductor cutters are half the size and weight of standard ratchet cutters
- Can get into confining workspaces like manholes and handholes
- Open in less than half the space required for long-handled ratcheting cutters
- Stampings on the jaws indicate application limits
- Reinforced-fiberglass handles are PVCcoated and protected by a vinyl sleeve
- Thick vinyl grips shield the handle ends and help worker keep a steady grasp

General

EU RoHS Indicator	No
Style	Guillotine Jaw
UPC	096359020271

Dimensions

Length	18 in
Weight	4.822 lb

Product Assets

[Catalogs - Cutters \(2150\)](#)

[Installation Manuals - CHANCE® Tools Manuals \(CENT_LTE_IOM_EN_00158\)](#)<LineBreak/>



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C4032980-SPEC-EN | REV 4/2023