



## Digital Phasing Tester, 40kV

By CHANCE Utility  
Catalog # [C4033370](#)

Large, backlit, direct-reading display easily determines phase relationships and approximate voltage, line-to-line or line-to-ground



\*Representative Image

### Features

- Large Digital Display with Backlight, Hold, and Sleep modes
- Two high-impedance components in fiberglass poles, each threaded for interchangeable probes
- 22-foot-long insulated flexible cable from voltmeter stores on reel on other pole
- 40kV Unit not suitable for Hi-Pot Testing
- Must be used with 2 Epoxiglas Insulating Universal Hotsticks (Not Included) of appropriate length

### General

EU RoHS Indicator	No
Style	Digital Display
UPC	096359368113

### Dimensions

Weight	14.5 lb
--------	---------

### Electrical Ratings

Withstand Voltage	40kV
-------------------	------

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Instruments and Meters \(2450\)](#)  
[Installation Manuals - CHANCE Digital Phasing Testers Operating Instructions \(P403-3407\)](#)  
[Video - CHANCE Meters and Instruments \(VI0955E\)](#)

### Related Products

[H18763 - Phasing Tester Case](#)  
[H18766P - Pigtail Hook Probe](#)  
[H18766S - Shepherd Hook Probe](#)  
[H18765 - Angle Probe](#)  
[H18766 - Straight Probe](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-C4033370-SPEC-EN | REV 8/2023