



## Class 2, Short-Lip Flexible Line Hose, 4.5'

By CHANCE Utility  
Catalog # [C4060295](#)



LINE HOSE, 1 1/4"X54" STRAIGHT, Much lighter in weight than other flexible dielectric cover-up, Chance Line Hose helps protect workers from accidental contact with conductors. In accordance with ASTM D 1050-90, Chance ozone/corona resistant thermoplastic elastomer offers excellent performance properties. It does not absorb water. Easy to handle and place The outer lip peels back with ease to open and start onto a conductor from either end. With a push at the other end, the full length slides on as the lips zip closed around the conductor. To remove each piece, open one end and strip the remainder off the conductor.

### Features

- High visibility orange color
- Type III ozone resistant material
- Class 2
- Maximum use voltage of 17kV phase-to-phase
- 100% electrically tested and visually inspected per ASTM D1050
- Date stamped
- Plain, both ends
- Style A

### General

Color	Orange
EU RoHS Indicator	No
Style	Straight on both ends
Type	III
UPC	096359020745

### Dimensions

Diameter	1.25 in
Length	54 in
Weight	3.597 lb

### Electrical Ratings

Voltage - Maximum	17 kV
Voltage Rating	Class 2 V

### Conductor Related

Conductor Size	1.25" diameter
----------------	----------------

### Logistics

Pallet Quantity	180
-----------------	-----

### Product Assets

[Catalogs - Cover-Up Equipment \(2400\)](#)  
[Literature - Cover-Up Care \(BR09003E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-C4060295-SPEC-EN | REV 8/2023