



Conductive Boot, Size 7

By CHANCE Utility
Catalog # [C4170624](#)

The Chance 8-inch leather conductive boot offers the lineman both comfort and protection. The boot meets all ANSI Specifications for conductive footwear.



*Representative Image

Features

- 8" leather conductive boot
- Offers linemen both comfort and protection
- Meets all ANSI Specifications for conductive footwear
- Has a leg harness with a black conductive sole
- A wire molded into the rubber leads up the back with the conductive rubber strap covering to a conductive snap fitting at the top of the boot
- An additional conductive boot strap is secured through a snap fitting from boot to conductive suit or to leg strap
- This connection again, has a wire built into a nylon and conductive rubber strap
- Boot upper is made of top quality, high oil content leather
- Water resistant
- Flexible and durable
- Finely-crafted stitching and brown finish
- Meets ANSI Class 75 steel toe footwear specifications (75 lb. crush strength)
- Has a flexible full stainless steel inner sole, 400 lb. test
- Heel counter is molded into the sole to prevent its pulling away
- Welt is neoprene, not rubber or leather, to resist cracking
- Sole is vulcanized under 20,000 pounds of pressure to the welt, not to upper
- Makes the sole more flexible and helps prevent it from separating from upper
- Tempered steel shank is built-in for proper arch support
- Meets ANSI Specifications Z41 for safety-toe footwear
- Manufactured to specification of less than 10,000 ohms from leg strap to boot heel
- 100% inspection/testing conducted on each boot as part of manufacturing process

Dimensions

Weight 6 lb

Product Assets

[Catalogs - Lineman's Accessories \(2550\)](#)
[Catalogs - Tools and Grounding Catalog Full](#)

General

UPC 096359468813



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C4170624-SPEC-EN | REV 8/2023

