



CHANCE® Ground Clamp, C-Type, Type I-Class B-Grade 5, 1.25in. Jaw Opening

By CHANCE Utility
Catalog # C6000065

CHANCE® Ground Clamp, C-Type, Type I-Class B-Grade 5, 1.25in. Jaw Opening



Features

- C-Type Ground Clamp
- Continuous Current 400A
- Fault Current 43kA for 15 cycles or 30kA for 30 cycles
- Main Line Range Max. 954MCM (1.20in.)
- Main Line Range Min. #6 Sol. CU (0.162in.)
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class B, Grade 5, Jaws Serrated
- Drilled and tapped ferrule boss for threaded ferrule

General

EU RoHS Indicator	No
Eye Screw/T-Handle	N/A
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	N/A
Handle Type	Eyescrew
Jaw Type	Serrated Jaws
Material	Aluminum
Terminal Connection Type	5/8"-11 Thread
UPC	096359023241

Dimensions

Jaw Opening Size - Maximum	1.2 in
Jaw Opening Size - Minimum	.162 in
Weight	1.225 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

Certifications and Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

Logistics

Pallet Quantity	25
-----------------	----

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C6000065-SPEC-EN | REV 8/2023