



Ground Clamp, Flat Face, Type I-Class B-Grade 3, 1.5" Jaw Opening

By CHANCE Utility
Catalog # [C6001735](#)

Ground Clamp, Flat Face, Type I-Class B-Grade 3, 1.5" Jaw Opening



*Representative Image

Features

- Tower & Flat-Face Ground Clamp
- Continuous Current 400A
- Fault Current 27kA for 15 cycles or 20kA for 30 cycles
- Main Line Range Max. 1.5" Angles or 1.5" Flat
- Main Line Range Min. 1/8"
- Jumper Range Max. 2/0 Grd. Cable w/ Threaded Stud
- Jumper Range Min. #2 Grd. Cable w/ Threaded Stud
- ASTM Type I, Class B, Grade 3
- Jaws Serrated
- Ferrule Threaded

General

| | |
|-------------------------------------|----------------|
| EU RoHS Indicator | No |
| Eye Screw/T-Handle | 250 in-lb |
| Installation Torque (in-lb) | |
| Ferrule Installation Torque (in-lb) | 250 in-lb |
| Handle Type | Eyescrew |
| Jaw Type | Serrated Jaws |
| Material | Aluminum |
| Terminal Connection Type | 5/8"-11 Thread |
| Thread Size | 5/8-11 UNC |
| UPC | 096359023883 |

Dimensions

| | |
|----------------------------|---------|
| Jaw Opening Size - Maximum | 1.5 in |
| Jaw Opening Size - Minimum | .125 in |
| Weight | 1.48 lb |

Electrical Ratings

| | |
|---------------------------------|--------------------------------|
| Current Rating | 300 A |
| Fault Current - 15 Cycles | 27000 A |
| Fault Current - 30 Cycles | 20000 A |
| Grounding Wire Capacity Maximum | 2/0 Cable w/ Threaded Terminal |
| Grounding Wire Capacity Minimum | #2 Cable w/ Threaded Terminal |

Certifications and Compliance

| | |
|----------------------------|--------------|
| Fault Current - ASTM Grade | ASTM Grade 3 |
|----------------------------|--------------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 20 |
|-----------------|----|

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C6001735-SPEC-EN | REV 8/2023