



Ground Clamp, Flat Face, Type I-Class B-Grade 5, 1.5" Jaw Opening

By CHANCE Utility
Catalog # [C6002232](#)

Ground Clamp, Flat Face, Type I-Class B-Grade 5, 1.5" Jaw Opening



Features

- Tower & Flat-Face Ground Clamp
- Continuous Current 400A
- Fault Current 43kA for 15 cycles or 30kA for 30 cycles
- Main Line Range Max. 1.5" Angles or 1.5" Flat
- Main Line Range Min. 1/8"
- Jumper Range Max. 4/0 Grd. Cable w/ Threaded Stud
- Jumper Range Min. #2 Grd. Cable w/ Threaded Stud
- ASTM Type I, Class B, Grade 5
- Jaws Serrated
- Ferrule Threaded

General

Eye Screw/T-Handle Installation Torque (in-lb)	250 in-lb
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Serrated Jaws
Material	Bronze
Terminal Connection Type	5/8"-11 Thread
Thread Size	5/8-11 UNC
UPC	096359024330

Dimensions

Jaw Opening Size - Maximum	1.5 in
Jaw Opening Size - Minimum	.125 in
Weight	2.94 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

Certifications and Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

Logistics

Carton Quantity	10
Pallet Quantity	480

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C6002232-SPEC-EN | REV 7/2023