



Ground Clamp, C-Type, Type I- Class A-ASTM Grade 5H, IEC Rating 35kA (15 Cycles), 2.0" Jaw Opening

By: CHANCE Lineman Tools & Equipment
Catalog # [C6002255](#)

Ground Clamp, C-Type, Type I-Class A-ASTM Grade 5H, IEC
Rating 35kA (15 Cycles), 2.0" Jaw Opening

Features

- C-Type Ground Clamp
- Continuous Current 400A
- Fault Current 47kA, X/R=30
- Main Line Range 2" O.D. Bus
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 5H
- IEC Rating 35kA (15 Cycles)
- Jaws Smooth
- Ferrule Threaded - Unshrouded Only

General

| | |
|---------------------------------------------------|----------------|
| Eye Screw/T-Handle Installation Torque (in-lb) | 250 in-lb |
| Ferrule Installation Torque (in- lb) | 250 in-lb |
| Handle Type | Eyescrew |
| Jaw Type | Smooth Jaws |
| Material | Aluminum |
| Terminal Connection Type | 5/8"-11 Thread |
| Thread Size | 5/8-11 UNC |
| UPC | 096359024354 |



Dimensions

| | |
|----------------------------|---------|
| Jaw Opening Size - Maximum | 2 in |
| Jaw Opening Size - Minimum | .162 in |
| Weight | 1.96 lb |

Electrical Ratings

| | |
|------------------------------------|-----------------------------------|
| Current Rating | 400 A |
| Fault Current - 15 Cycles | 47000 A |
| Fault Current - 30 Cycles | 30000 A |
| Grounding Wire Capacity Maximum | 4/0 Cable w/ Threaded Terminal |
| Grounding Wire Capacity Minimum | #2 Cable w/ Threaded Terminal |

Certifications and Compliance

| | |
|----------------------------|---------------|
| Fault Current - ASTM Grade | ASTM Grade 5H |
|----------------------------|---------------|

Logistics

| | |
|-----------------|-----|
| Pallet Quantity | 480 |
|-----------------|-----|

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C6002255-SPEC-EN | REV 4/2023