



CHANCE® 15kV 12ft. 1/0 Rubber Glove Jumper Set, 25kV Orange Clamps

By CHANCE Utility
Catalog # [C6010172](#)



CHANCE® 15kV 12ft. 1/0 Rubber Glove Jumper Set, 25kV Orange Clamps

Features

- Designed and tested to ASTM F2321
- Complete set rated to 15kV
- Includes G4765 longer 25kV Rubber Glove Jumper Clamps and 12ft of S10044 1/0 15kV Jumper Cable
- Continuous current rating of 260 amps
- Conductor range of #6 CU to 795 ACSR
- Used for bypassing work areas when equipment is under repair, upgrading lines, and making temporary or emergency repairs
- Clamps have 7-1/2" below the handguard
- Adequate rubber gloves must be worn when installing or removing jumper clamps

General

EU RoHS Indicator	No
Style	Rubber Glove Applied
UPC	096359024606

Dimensions

Length	12 ft
Length - Jumper	144 in
Weight	15.68 lb

Electrical Ratings

Amperage Rating	260
Current Rating	260 A
Voltage - Maximum	15 kV
Voltage Rating	15 kV

Conductor Related

Conductor Diameter (Main) - Maximum	0.88 in
Conductor Diameter (Main) - Minimum	0.162 in
Conductor Size	1/0 AWG

Logistics

Pallet Quantity	16
-----------------	----

Product Assets

[Catalogs - Jumpers & Load Pickup Tools \(2300\)](#)



A proud member of the Hubbell Family.