



15 kV, 110 kV BIL, Type C Standard Porcelain Cutout w/300A Solid Blade

By Chance
Catalog # [C710133L](#)

15 kV, 110 kV BIL, Standard Type C Porcelain Cutout with a 300A solid blade, large eyebolt connector and no bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

| | |
|---------------------------|--------------|
| Bracket Type | No Bracket |
| Catalog Number | C710133L |
| Description - Replacement | T710-133T |
| Fuse Holder Type | Cutout |
| UPC | 096359029311 |

Dimensions

| | |
|--------|----------|
| Weight | 6.507 lb |
|--------|----------|

Electrical Ratings

| | |
|--|-------------------|
| BIL | 110 kV |
| Creep and Leakage Distance | 8.7" (220mm) |
| Current Rating | 300 A |
| Reference Voltage Limit - Minimum | Thru 14.4kV |
| Temperature Rise - Max. at 300A | 38° C |
| Voltage - Maximum | 15 kV |
| Voltage - Radio Interference | Ambient @ 9.41kV |
| Voltage Rating | 15 kV |
| Withstand Current - Short Time (10 cycles) | 12,000 Amps Asym. |

Logistics

| | |
|------------------|----|
| Pallet Quantity | 54 |
| Standard Package | 1 |

Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Sales Drawings - 110 KV BIL Cutout](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C710133L-SPEC-EN | REV 6/2024