



## 27 kV, 150 kV BIL, Type C Standard Porcelain Cutout w/200A 10kAIC fuseholder

By CHANCE Utility  
Catalog # [C710342EX](#)

27 kV, 150 kV BIL, Standard Type C Porcelain Cutout with a 200A, 10kAIC fuseholder, small eyebolt connector and an extended NEMA "B" crossarm bracket.



\*Representative Image

### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

### General

|                                       |                                |
|---------------------------------------|--------------------------------|
| Bracket Type                          | Extended NEMA "B" for crossarm |
| Corrosion Resistant?                  | No                             |
| Description - Replacement Fuse Holder | T710-342T                      |
| Type                                  | Cutout                         |

### Dimensions

|        |          |
|--------|----------|
| Weight | 30.51 lb |
|--------|----------|

### Electrical Ratings

|                                   |   |
|-----------------------------------|---|
| BIL                               | 150 kV  |
| Creep and Leakage Distance        | 17.3" (440mm)                                     |
| Current Rating                    | 200 A   |
| Fuselink Current Range            | 140A to 200A                                      |
| Reference Voltage Limit - Minimum | No Restrictions thru 24.9kV;<br>*26.4 thru 34.5kV |
| Temperature Rise - Max. at 300A   | 35° C   |
| Voltage - Maximum                 | 27 kV   |
| Voltage - Radio Interference      | Ambient @22kV                                     |
| Voltage Rating                    | 27 kV   |

### Logistics

|                  |       |
|------------------|-------|
| Pallet Quantity  | 42 EA |
| Standard Package | 1     |

### Product Assets

[Catalogs - Type C-Porcelain Cutouts \(10A\)](#)  
[Installation Manuals - Standard Cutout Installation Instructions](#)  
[Literature - SF11036E\\_HPS CHANCE RUS Cutout Listing](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Sales Drawings - 150KV BIL Cutout \(SA710-3\)](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-C710342EX-SPEC-EN | REV 1/2024