



# 36 kV, 170 kV BIL, Type C Standard Porcelain Cutout w/200A 12kAIC fuseholder

By Chance  
Catalog # [C710643LDM](#)

36 kV, 170 kV BIL, Standard Type C Porcelain Cutout with a 200A, 12kAIC fuseholder, large eyebolt connector and a D-shape pole mounting bracket.

## Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 – 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

## General

Bracket Type	D-shape for pole mounting
Catalog Number	C710643LDM
Corrosion Resistant?	No
Description - Replacement	T710-643TM
Fuse Holder	
Type	Cutout

## Dimensions

Weight	36.98 lb
--------	----------

## Electrical Ratings

BIL	170 kV
-----	--------



Creep and Leakage Distance	26" (660mm)
Current Rating	200 A
Fuselink Current Range	140A to 200A - removable buttonhead fuse link only
Voltage - Maximum	27 kV
Voltage Rating	36 kV

## Logistics

Pallet Quantity	24 EA
Standard Package	1

## Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Sales Drawings - 170KV BIL Cutout \(660MM\)](#)
- [Specifications - C710643LDM](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand