



36 kV, 170 kV BIL, Type C Standard Porcelain Cutout / Arrester Combination w/300A Solid Blade

By Chance

Catalog # [C71DP733ED](#)

36 kV, 170 kV BIL, Standard Type C Porcelain Cutout / Arrester Combination with a 300A, 12kAIC solid blade, small eyebolt connector and a D-shape pole mounting bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

General

Bracket Type	D-shape for pole mounting
Catalog Number	C71DP733ED
Corrosion Resistant?	No
Description - Replacement	T710-733T
Fuse Holder Type	Cutout

Electrical Ratings

BIL	170 kV
Creep and Leakage Distance	28.4" (720mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 34.5kV
Voltage - Maximum	36 kV
Voltage Rating	36 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

Logistics

Pallet Quantity	18 EA
Standard Package	1

Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - 170 KV BIL \(720MM\) Cutout/ Arrester](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand