



15/27 kV, 125 kV BIL, Type C Linkbreak Porcelain Cutout w/100A 12kAIC fuseholder

By Chance
Catalog # [C720213L](#)

15/27 kV, 125 kV BIL, Linkbreak Type C Porcelain Cutout with a 100A, 12kAIC fuseholder, large eyebolt connector and no bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	No Bracket
Catalog Number	C720213L
Description - Replacement	T720-213T
Fuse Holder	
Type	Cutout
UPC	096359630210

Dimensions

Weight	20.91 lb
--------	----------

Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 14.9kV; *20.8 thru 24.9kV
Temperature Rise - Max. at 300A	33° C
Voltage - Radio Interference	Ambient @15.66kV
Voltage Rating	15/27 kV

Logistics

Pallet Quantity	48 EA
Standard Package	1

Product Assets

- [Catalogs - Type C-Porcelain Cutouts](#)
- [Installation Manuals - Link Break Cutout Installation Instructions](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Sales Drawings - Cutout, Linkbreak 125 KV BIL](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C720213L-SPEC-EN | REV 6/2024