



22/36.4 kV, 150 kV BIL, Type C Linkbreak Porcelain Cutout w/100A 12kAIC fuseholder

By Chance

Catalog # [C720313LZS](#)

22/36.4 kV, 150 kV BIL, Linkbreak Type C Porcelain Cutout with a 100A, 12kAIC fuseholder, large eyebolt connector and no bracket.

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	No Bracket
Catalog Number	C720313LZS
Corrosion Resistant?	Yes
Description - Replacement	T720-313T
Fuse Holder Type	Cutout

Dimensions

Weight	26.71 lb
--------	----------

Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 20.8kV; *22.8 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	22/36.4 kV



Logistics

Pallet Quantity	42 EA
Standard Package	1

Product Assets

[Catalogs - Type C-Porcelain Cutouts](#)
[Installation Manuals - Link Break Cutout Installation Instructions](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
[Sales Drawings - Cutout, Linkbreak 125 KV BIL](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C720313LZS-SPEC-EN | REV 6/2024