



## 22/36.4 kV, 150 kV BIL, Type C Linkbreak Porcelain Cutout w/100A 12kAIC fuseholder

By Chance  
Catalog # [C720313PDS](#)

22/36.4 kV, 150 kV BIL, Linkbreak Type C Porcelain Cutout with a 100A, 12kAIC fuseholder, parallel-groove connector and a D-shape pole mounting bracket.



### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

### General

Bracket Type	D-shape for pole mounting
Catalog Number	C720313PDS
Corrosion Resistant?	Yes
Description - Replacement	T720-313T
Fuse Holder Type	Cutout

### Dimensions

Weight	34.4 lb
--------	---------

### Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 20.8kV; *22.8 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	22/36.4 kV

### Logistics

Pallet Quantity	42 EA
Standard Package	1

### Product Assets

[Catalogs - Type C-Porcelain Cutouts](#)  
[Installation Manuals - Link Break Cutout Installation Instructions](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)  
[Sales Drawings - Cutout, Linkbreak 125 KV BIL](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-C720313PDS-SPEC-EN | REV 6/2024