



22/36.4 kV, 170 kV BIL, Type C
Linkbreak Porcelain Cutout
w/100A 12kAIC fuseholder

By CHANCE Utility
Catalog # C720613PX

22/36.4 kV, 170 kV BIL, Linkbreak Type C Porcelain Cutout with a 100A, 11.2kAIC fuseholder, parallel-groove connector and an extended NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 – 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material

General

Bracket Type	Extended NEMA "B" for crossarm
Corrosion Resistant?	No
Description - Replacement Fuse Holder	T720-613T
Type	Cutout

Dimensions

Weight	33.38 lb
--------	----------

Electrical Ratings

BIL	170 kV
Creep and Leakage Distance	26" (660mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 20.8kV; *22.8 thru 34.5kV
Voltage Rating	22/36.4 kV

Logistics

Standard Package	1
------------------	---

Product Assets

- Catalogs - Type C-Porcelain Cutouts (10A)
- Installation Manuals - Link Break Cutout Installation Instructions
- Literature - SF11036E_HPS CHANCE RUS Cutout Listing
- Literature - Switching Line Card_FAQ_2019
- Sales Drawings - Cutout, Linkbreak 125 KV BIL (SA720-6)
- Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience (VI10004E)
- Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality (VI10005E)



A proud member of the Hubbell Family.