



REGULAR DUTY ALUMINUM EQUIPMENT PLATFORM, 12ft MOUNTING SPACE BETWEEN POLES, w/ONE WALKWAY



By Chance
Catalog # [CP122WKY](#)

Aluminum Extra Heavy Duty equipment platform with 12' inside pole face to face spacing. The platform width is 42" and includes a 41" wide walkway on one side with hand rails. Walkway planking is not included and sourced seperately. Platform attaches to pole with eight 3/4" machine bolts (four per side) that are purchased seperately.

Features

- Light-weight 6061-T6 aluminum for supporting heavy equipment such as transformers and regulators
- Factory assembled and shipped on removable wheels for mobility to the job site.
- Rated for three vertical loads of 2,000 lbs. each or one center load of 5,000 lbs.

General

Catalog Number	CP122WKY
EU RoHS Indicator	No
UPC	096359533078

Dimensions

Distance From Pole	N/A
--------------------	-----

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Product Assets

- [Catalogs - Aluminum Hardware & Apitong Wood](#)
- [Installation Manuals - INSTRUCTIONS FOR REGULAR DUTY ALUMINUM PLATFORMS](#)
- [Sales Drawings - Platform, Aluminum](#)
- [Specifications - CP122WKY](#)