



Extension, RS2875.203, 14/14 X 7ft

By Chance
Catalog # [CRSEADFF07](#)

Round Shaft Extension 7' long 2.875" 0.203" Wall Diameter 14" - 14" Helices.



Features

- Round Shaft Lead Sections are assembled to Round Shaft Extension with through bolt(s).
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of pile can be determined by measuring installation torque
- Bolt and nut are assembled to extension at the factory

Application

Helical Anchoring

General

Catalog Number	CRSEADFF07
Coating	Galvanized, ASTM A-153
Number of Helices	2
Pipe Type	Wall Round Pipe
Style	Round Shaft Helical Piles
	RS2875.203
Torque Rating	5500 ft-lbs
Type	Anchor Extensions

Dimensions

Anchor Helix Diameter(s)	14 in - 14 in
Foundation Diameter	<ul style="list-style-type: none">• 2.875 in• 0.203 in
Foundation Length	84 in
Length	84 in
Weight	75 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Foundations & Installing Tools for Transmission & Substations](#)
- [Installation Manuals - Helical Piles Installation Instructions](#)
- [Literature - Helical Piles and Guy Anchors Structures](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Transmission & Substation Design Request Form](#)
- [Literature - Helical Foundation GA Coast](#)
- [Sales Drawings - Multi-Helix Leads And Helical Extensions](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - CRSEADFF07](#)
- [Video - CHANCE Round Shaft Anchor Installation](#)



A Hubbell brand