



Extension, RS3500.300, 14/14/14 X 10ft

By Chance

Catalog # [CRSECDDDF10CU](#)

Round Shaft Extension 10' long 3.5" Diameter 14" - 14" - 14"
Helices.



Features

- Round Shaft Lead Sections are assembled to Round Shaft Extension with through bolt(s).
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of pile can be determined by measuring installation torque
- Bolt and nut are assembled to extension at the factory

General

Application	Helical Anchoring
Coating	Galvanized, ASTM A-153
Number of Helices	3
Pipe Type	Round Pipe
Style	Round Shaft Helical Piles RS3500.300
Torque Rating	13000 ft-lbs
Type	Anchor Extensions

Dimensions

Anchor Helix Diameter(s)	14 in - 14 in - 14 in
Foundation Diameter	3.5 in
Foundation Length	120 in
Length	120 in
Weight	173 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- [Case Studies - NE Power Coop Sub Foundations](#)
- [Installation Manuals - Chance Helical Pile/Anchor Installation Log Form to record installation details of Chance helical piles.](#)
- [Literature - Transmission & Substation Design Request Form](#)
- [Literature - Helical Piles and Guy Anchors Structures](#)
- [Literature - New Construction Helical Pile Foundation System](#)
- [Sales Drawings - RS3500.300 LEADS AND EXTENSIONS](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Round Shaft Anchor Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-CRSEDDDF10CU-SPEC-EN | REV 6/2024