



Extension, RS3500.300, 10ft

By CHANCE Utility
Catalog # [CRSECF10CU](#)

Round Shaft Extension 10' long 3.5" Diameter.



Features

- Round Shaft Lead Sections are assembled to Round Shaft Extension with through bolt(s).
- Hot dipped galvanized per ASTM A153
- Capacity of pile can be determined by measuring installation torque
- Bolt and nut are assembled to extension at the factory

Application

Helical Anchoring

General

Coating	Galvanized, ASTM A-153
Pipe Type	Round Pipe
Style	Round Shaft Helical Piles RS3500.300
Torque Rating	13000 ft-lbs
Type	Anchor Extensions
UPC	096359713777

Dimensions

Foundation Length	120 in
Length	120.000 in
Weight	115.000 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Case Studies - NE Power Coop Sub Foundations \(CH06015E\)](#)
- [Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- [Literature - Helical Piles and Guy Anchors Structures \(BR06082E\)](#)
- [Literature - Transmission & Substation Design Request Form \(SF06126E_1120\)](#)
- [Sales Drawings - RS3500.300 LEADS AND EXTENSIONS](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Round Shaft Anchor Installation \(VI0654E\)](#)



A proud member of the Hubbell Family.