



LEAD, RS2875.203, 8 /10 X 5ft

By Chance
Catalog # [CRSLAABFF05](#)

Round Shaft Lead Section 5' long 2.875" 0.203" Wall Diameter 8" - 10" Helices.



Features

- Round Shaft Lead Sections are assembled to Round Shaft Extension with through bolt(s).
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of pile can be determined my measuring installation torque

Application

Helical Anchoring

General

Catalog Number	CRSLAABFF05
Coating	Galvanized, ASTM A-153
Number of Helices	2
Pipe Type	Wall Round Pipe
Style	Round Shaft Helical Piles
	RS2875.203
Torque Rating	5500 ft-lbs
Type	Lead Sections

Dimensions

Anchor Helix Diameter(s)	8 in - 10 in
Foundation Diameter	• 2.875 in

	• 0.203 in
Foundation Length	60 in
Length	60 in
Weight	45 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Foundations & Installing Tools for Transmission & Substations](#)
- [Installation Manuals - Type RS2875.203 Helical Pile](#)
- [Installation Manuals - Helical Piles Installation Instructions](#)
- [Installation Manuals - Type RS2875.203 Helical Pile Building Code](#)
- [Literature - Helical Piles and Guy Anchors Structures](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Transmission & Substation Design Request Form](#)
- [Literature - Helical Foundation GA Coast](#)
- [Sales Drawings - Multi-Helix Leads And Helical Extensions](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - CRSLAABFF05](#)
- [Video - CHANCE Round Shaft Anchor Installation](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools](#)