



# LEAD, RS2875.203, 12 X 7ft

By Chance  
Catalog # [CRSLACFFF07](#)

Round Shaft Lead Section 7' long 2.875" 0.203" Wall Diameter  
12" Helices.



## Features

- Round Shaft Lead Sections are assembled to Round Shaft Extension with through bolt(s).
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of pile can be determined my measuring installation torque

## Application

Helical Anchoring

## General

Catalog Number	CRSLACFFF07
Coating	Galvanized, ASTM A-153
Number of Helices	1
Pipe Type	Wall Round Pipe
Style	Round Shaft Helical Piles RS2875.203
Torque Rating	5500 ft-lbs
Type	Lead Sections

## Dimensions

Anchor Helix Diameter(s)	12 in
Foundation Diameter	<ul style="list-style-type: none"><li>• 2.875 in</li></ul>

	<ul style="list-style-type: none"><li>• 0.203 in</li></ul>
Foundation Length	84 in
Length	84 in
Weight	54 lb

## Logistics

Standard Package	1
------------------	---

## Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Foundations & Installing Tools for Transmission & Substations](#)
- [Installation Manuals - Type RS2875.203 Helical Pile](#)
- [Installation Manuals - Helical Piles Installation Instructions](#)
- [Installation Manuals - Type RS2875.203 Helical Pile Building Code](#)
- [Literature - Helical Piles and Guy Anchors Structures](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Transmission & Substation Design Request Form](#)
- [Literature - Helical Foundation GA Coast](#)
- [Sales Drawings - Multi-Helix Leads And Helical Extensions](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - CRSLACFFF07](#)
- [Video - CHANCE Round Shaft Anchor Installation](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools](#)



A Hubbell brand