



LEAD, RS2875.276, 10/12/14/14 X 10ft

By Chance
Catalog # [CRSLBBCDD10](#)

Round Shaft Lead Section 10' long 2.875" 0.276" Wall Diameter
10" - 12" - 14" - 14" Helices.



*Representative Image

Features

- Round Shaft Lead Sections are assembled to Round Shaft Extension with through bolt(s).
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of pile can be determined my measuring installation torque

Application

Helical Anchoring

General

Catalog Number	CRSLBBCDD10
Coating	Galvanized, ASTM A-153
Number of Helices	4
Pipe Type	Wall Round Pipe
Style	Round Shaft Helical Piles
	RS2875.276
Torque Rating	8000 ft-lbs
Type	Lead Sections

Dimensions

Anchor Helix Diameter(s)	10 in - 12 in - 14 in - 14 in
--------------------------	-------------------------------

Foundation Diameter	<ul style="list-style-type: none">• 2.875 in• 0.276 in
Foundation Length	120 in
Length	120 in
Weight	118 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Foundations & Installing Tools for Transmission & Substations](#)
- [Installation Manuals - Type RS2875.276 Helical Pile Building Code](#)
- [Installation Manuals - Helical Piles Installation Instructions](#)
- [Installation Manuals - Type RS2875.276 Helical Pile](#)
- [Literature - Helical Piles and Guy Anchors Structures](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Transmission & Substation Design Request Form](#)
- [Literature - Helical Foundation GA Coast](#)
- [Sales Drawings - Multi-Helix Leads And Helical Extensions](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - CRSLBBCDD10](#)
- [Video - CHANCE Round Shaft Anchor Installation](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools](#)



A Hubbell brand