



LEAD, RS3500.300, 8/10/12 X 7ft

By Chance
Catalog # [CRSLCABCF07](#)

Round Shaft Lead Section 7' long 3.5" Diameter 8" - 10" - 12" Helices.



Features

- Round Shaft Lead Sections are assembled to Round Shaft Extension with through bolt(s).
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of pile can be determined my measuring installation torque

Application

Helical Anchoring

General

Catalog Number	CRSLCABCF07
Coating	Galvanized, ASTM A-153
Number of Helices	3
Pipe Type	Round Pipe
Style	Round Shaft Helical Piles RS3500.300
Torque Rating	13000 ft-lbs
Type	Lead Sections
UPC	096359645290

Dimensions

Anchor Helix Diameter(s)	8 in - 10 in - 12 in
Foundation Diameter	3.5 in
Foundation Length	84 in
Length	84 in

Weight 73 lb

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Standard Package 1

Product Assets

- [Case Studies - NE Power Coop Sub Foundations](#)
- [Catalogs - Anchor Tools](#)
- [Catalogs - Foundations & Installing Tools for Transmission & Substations](#)
- [Installation Manuals - Helical Piles Installation Instructions](#)
- [Installation Manuals - Type RS3500.300 Helical Pile Building Code](#)
- [Installation Manuals - Type RS3500.300 Helical Pile](#)
- [Literature - Helical Piles and Guy Anchors Structures](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Transmission & Substation Design Request Form](#)
- [Literature - Helical Foundation GA Coast](#)
- [Sales Drawings - Leads And Extensions](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - CRSLCABCF07](#)
- [Video - CHANCE Round Shaft Anchor Installation](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools](#)



A Hubbell brand