



LEAD, RS4500.337, 8 X 10ft

By Chance
Catalog # [CRSLDAFFF10](#)

Round Shaft Lead Section 10' long 4.5" Diameter 8" Helices.



Features

- Round Shaft Lead Sections are assembled to Round Shaft Extension with through bolt(s).
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of pile can be determined by measuring installation torque

Application

Helical Anchoring

General

Catalog Number	CRSLDAFFF10
Coating	Galvanized, ASTM A-153
Number of Helices	1
Pipe Type	Round Pipe
Style	Round Shaft Helical Piles
	RS4500.337
Torque Rating	23000 ft-lbs
Type	Lead Sections

Dimensions

Anchor Helix Diameter(s)	8 in
Foundation Diameter	4.5 in
Foundation Length	120 in
Length	120 in
Weight	170 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- [Case Studies - Helical Pile Article](#)
- [Catalogs - Anchor Tools](#)
- [Catalogs - Foundations & Installing Tools for Transmission & Substations](#)
- [Installation Manuals - Helical Piles Installation Instructions](#)
- [Literature - Helical Piles and Guy Anchors Structures](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Transmission & Substation Design Request Form](#)
- [Literature - Helical Foundation GA Coast](#)
- [Sales Drawings - RS4500.337 Leads And Helical Extensions](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - CRSLDAFFF10](#)
- [Video - CHANCE Round Shaft Anchor Installation](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools](#)