



# LEAD, RS6625.280, 12 X 7ft box coupler

By Chance  
Catalog # [CRSLECFFF07](#)



Round Shaft Lead Section 7' long 6.63" Diameter 12" Helices.

## Features

- Round Shaft Lead Sections are assembled to Round Shaft Extension with through bolt(s).
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of pile can be determined my measuring installation torque

## Application

Helical Anchoring

## General

Catalog Number	CRSLECFFF07
Coating	Galvanized, ASTM A-153
Number of Helices	1
Pipe Type	Round Pipe
Style	Round Shaft Helical Piles
	RS6625.280
Torque Rating	40000 ft-lbs
Type	Lead Sections

## Dimensions

Anchor Helix Diameter(s)	12 in
Foundation Diameter	6.63 in
Foundation Length	84 in
Length	84 in
Weight	141 lb

## Logistics

Standard Package	1
------------------	---

## Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Foundations & Installing Tools for Transmission & Substations](#)
- [Installation Manuals - Helical Piles Installation Instructions](#)
- [Literature - Helical Piles and Guy Anchors Structures](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Transmission & Substation Design Request Form](#)
- [Literature - Helical Foundation GA Coast](#)
- [Sales Drawings - Leads](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - CRSLECFFF07](#)
- [Video - CHANCE Round Shaft Anchor Installation](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools](#)



A Hubbell brand