



LEAD, RS6625.280, 14 X 15ft box coupler

By Chance
Catalog # [CRSLEDFFF15](#)



Round Shaft Lead Section 15' long 6.63" Diameter 14" Helices.

Features

- Round Shaft Lead Sections are assembled to Round Shaft Extension with through bolt(s).
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of pile can be determined my measuring installation torque

Application

Helical Anchoring

General

Catalog Number	CRSLEDFFF15
Coating	Galvanized, ASTM A-153
Number of Helices	1
Pipe Type	Round Pipe
Style	Round Shaft Helical Piles
	RS6625.280
Torque Rating	40000 ft-lbs
Type	Lead Sections

Dimensions

Anchor Helix Diameter(s)	14 in
Foundation Diameter	6.63 in
Foundation Length	180 in
Length	126 in
Weight	297 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Foundations & Installing Tools for Transmission & Substations](#)
- [Installation Manuals - Helical Piles Installation Instructions](#)
- [Literature - Helical Piles and Guy Anchors Structures](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Transmission & Substation Design Request Form](#)
- [Literature - Helical Foundation GA Coast](#)
- [Sales Drawings - RS4500.337 Leads And Helical Extensions](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - CRSLEDFFF15](#)
- [Video - CHANCE Round Shaft Anchor Installation](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools](#)



A Hubbell brand