



PORCELAIN SPOOL INSULATOR, ANSI 53-2, GRAY

By CHANCE Utility
Catalog # [DE4S5](#)

Spool insulators are used with spool bolts (upset bolts), insulator clevises and secondary racks for neutral and secondary applications. Industry slant is pineapple.



Features

- Low Frequency Flashover: Dry: 25kV Wet: 12kV Vertical, 15kV Horizontal
- 3,000 lbs. minimum ultimate tensile strength

General

Material	Wet-process Porcelain
Tensile Strength	3000 lb.
UPC	096359369462

Dimensions

Distance From Pole	N/A
Weight	1.19 lb

Certifications and Compliance

Industry Standard(s)	ANSI 53-2
----------------------	-----------

Logistics

Pallet Quantity	1440
-----------------	------

Product Assets

[Catalogs - Bracket, Pole Top for Post Type Insulators \(5-53Supp20-23\)](#)

[Catalogs - Pole Line Hardware Supplements \(5-53Supp1-19\)](#)

[Sales Drawings - Spool Insulator, 53-2 \(SADE4S5\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-DE4S5-SPEC-EN | REV 4/2023