



Medium Duty Fiberglass Deadend Arm, 60"

By CHANCE Utility
Catalog # [DEM60SPEB](#)



Deadend Arm, 2-1/2" x 60" Medium Duty Fiberglass. Base and end fittings are aluminum alloy.

*Representative Image

General

Duty	Medium Duty
Material	Fiberglass
Strength Rating - Minimum Ultimate, Longitudinal (L)	3,000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	2,400 lb
Type	Fiberglass Deadend Arm
UPC	096359360148

Dimensions

Diameter - Rod / Tube	2.5 in
Length	60.00 in
Mounting Bolt Spacing	10.00 in
Weight	26.8 lb

Logistics

Pallet Quantity	24
Standard Package	2

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-64\)](#)
[Sales Drawings - Medium Duty Deadend Arms W/ Eye \(SADEMxxSPEB\)](#)
[Technical Solutions - CH-DEM60SPEB-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-DEM60SPEB-SPEC-EN | REV 1/2024