



# BOLT, MACHINE, SQ HEAD, 1/2in x 16in



By Chance  
Catalog # [DF2B16](#)

Square head machine bolt for utility pole and crossarm construction. Rated for 7,800 lbs. tensile strength. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

### Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1

### General

Catalog Number	DF2B16
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Steel
Tensile Strength	7800 lb.
Type	Machine Bolts
UPC	096359369592

### Dimensions

Diameter	0.5 in
Diameter (Fraction)	1/2 in

Distance From Pole	N/A
Length	16 in
Length - Threaded Area	6 in
Weight	0.79 lb

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

### Logistics

Carton Quantity	50
Pallet Quantity	1500

### Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - Bolts, Machine 1/2"](#)
- [Specifications - DF2B16](#)