



BOLT, MACHINE, SQ HEAD, 3/4in x 7in

By Chance
Catalog # [DF4B7](#)



Square head machine bolt for utility pole and crossarm construction. Rated for 18,350 lbs. tensile strength. Includes one assembled square nut, cone point and 4" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1
- RUS listed, c - Bolt, machine

General

Catalog Number	DF4B7
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Steel
Tensile Strength	18350 lb.
Type	Machine Bolts
UPC	096359369646

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Distance From Pole	N/A
Length	7 in
Length - Threaded Area	3
Weight	1.1 lb

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

Logistics

Pallet Quantity	1800
-----------------	------

Product Assets

[Catalogs - Thermal Diffusion Galvanizing](#)
[Sales Drawings - GALV. 3/4" DIA. SQ. HD. BOLT AND SQ. NUT ASSEMBLY](#)