



4-WAY, ADJUSTABLE POLE BAND for 7-1/2in to 12in POLE DIAMETERS

By Chance
Catalog # [DG17B2](#)



4-way, adjustable pole band for pole guys and insulator attachment. Band segments are 1/4" x 4" steel and connecting bolt size is 3/4" x 10". Band is shipped unassembled. Connecting links and rollers are ordered seperately.

Features

- 9/16" hole in each segment for lag or through bolt
- Galvanized per ASTM A-153

General

Catalog Number	DG17B2
Coating	Galvanized, ASTM A-153
Diameter - Pole	7.50 in X 12.00 in
EU RoHS Indicator	No
Material	Steel
Size	0.25 in X 4.00 in
UPC	096359369806

Dimensions

Diameter - Lag Screw - Maximum	0.52 in
Diameter - Stud	0.75 in X 6.00 in
Distance From Pole	N/A
Weight	15.19 lb

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	-----------------------------------------------------

Logistics

Pallet Quantity	128
-----------------	-----

Product Assets

[Sales Drawings - Adjustable Pole Band](#)
[Specifications - DG17B2](#)



A Hubbell brand