



TRANSFORMER BRACKET, 3-POSITION, STEEL RACK STYLE with NEMA A LUG SPACING

By Chance
Catalog # [DT6C1](#)

Welded Frame



Features

- Rated for 2,000 lbs. maximum capacity per position simultaneous loading
- Galvanized steel per ASTM A-153

General

Catalog Number	DT6C1
Coating	Galvanized, ASTM A-153
Material	Steel
Type	Bolted Pole Mount Bracket
UPC	096359370512

Dimensions

Dimensions	30.000 in x 11.750 in x 21.000 in
Distance From Pole	N/A
Height	21 in
Length	30 in
Weight	31.36 lb
Width	11.75 in

Logistics

Pallet Quantity	20
-----------------	----

Product Assets

[Catalogs - Pole Line Hardware Supplements](#)
[Sales Drawings - Cluster Mounting Bracket](#)