



NOB-LOC TYPE UNDERGROUND CABLE RACK, 28-3/4in LENGTH

By Chance
Catalog # DU1B28

Cable racking mounts to wall with expansion or anchor bolts for support of cable in underground vault applications. Support hooks (stanchions) and insulator pads complete the installation and are purchased separately.



*Representative Image

Features

- 3/8" x 1-3/4" steel
- Two 9/16" x 7/8" dia. mounting holes on 13" centers
- Five support hook holes
- Hot dip galvanized per ASTM A-153
- In compliance with ANSI C135.35 standard

General

Catalog Number	DU1B28
Coating	Galvanized, ASTM A-153
Material	Steel
Number of Holes	5
UPC	096359370642

Dimensions

Dimensions	28.75 in x 2.000 in x 2.000 in
Distance From Pole	N/A
Height	2 in
Length	28.75 in
Weight	4.9 lb
Width	2 in

Certifications And Compliance

Industry Standard(s)	ANSI C135.35
----------------------	--------------

Logistics

Pallet Quantity	300
-----------------	-----

Product Assets

[Catalogs - Pole Line Hardware Supplements](#)
[Sales Drawings - Underground Rack](#)