



NOB-LOC TYPE UNDERGROUND CABLE RACK, 56-3/4in LENGTH

By Chance
Catalog # DU1B30

Cable racking mounts to wall with expansion or anchor bolts for support of cable in underground vault applications. Support hooks (stanchions) and insulator pads complete the installation and are purchased separately.



Features

- 3/8" x 1-3/4" steel
- Two 9/16" x 7/8" dia. mounting holes on 13" centers
- 13 support hook holes
- Hot dip galvanized per ASTM A-153
- In compliance with ANSI C135.35 standard

General

Catalog Number	DU1B30
Coating	Galvanized, ASTM A-153
Material	Steel
Number of Holes	13
UPC	096359370673

Dimensions

Dimensions	56.75 in x 9.000 in x 9.000 in
Distance From Pole	N/A
Height	9 in
Length	56.75 in
Weight	9.8 lb
Width	9 in

Certifications And Compliance

Industry Standard(s)	ANSI C135.35
----------------------	--------------

Logistics

Pallet Quantity	200
-----------------	-----

Product Assets

[Catalogs - Pole Line Hardware Supplements](#)
[Sales Drawings - Underground Rack](#)