



# Anchor, PISA 7, 8in, 1in threads

By Chance  
Catalog # [E1021223](#)

Pisa 7 Anchor Helix; 7,000 Ft Lbs ( 9,492 N-M), 8" (203 mm)  
Helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.

## Features

- Installed with Chance anchor wrench C3031064 or C3030983
- Anchor has curvilinear leading edges to help penetrate rocky soils and to reduce damage during installation
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

## Application

Helical Anchoring

## General

Catalog Number	E1021223
Coating	Painted
Number of Helices	1
Torque Rating	7000 ft-lbs
Type	Anchor Helix
UPC	096359232759

## Dimensions

Anchor Helix Diameter(s)	8 in
Anchor Hub Size	1.5 in
Dimensions	10.000 in x 8.000 in x 8.000 in
Height	8 in
Length	10 in
Rod Diameter	<ul style="list-style-type: none"><li>• 0.75</li><li>• 1 in</li></ul>



Weight	10.417 lb
Width	8 in

## Certifications And Compliance

Buy America(n) Qualified	BABA Compliant (All status valid till December 2025)
--------------------------	--

## Logistics

Pallet Quantity	180
Standard Package	4

## Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Anchors](#)
- [Catalogs - Dependable Anchoring Solutions](#)
- [Catalogs - Communications Catalog](#)
- [Installation Manuals - Holding Capacity Chart - PISA Anchors](#)
- [Installation Manuals - TD06131E\\_PISA\\_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - How to Match Anchors and Installing Wrenches](#)
- [Sales Drawings - Pisa-6 & Pisa-7 Helix And Core Ass'y](#)
- [Specifications - E1021223](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)



A Hubbell brand