



## Anchor, PISA Mid-Strength, 10in, 1in threads

By CHANCE Utility  
Catalog # [E1021633](#)

Mid- Strength Anchor Helix; 6,000 Ft Lbs ( 8,136 N-M), 10" (254 mm) Helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.



\*Representative Image

### Features

- Installed with Chance anchor wrench C1021583
- Anchor has curvilinear leading edges to help penetrate rocky soils and to reduce damage during installation
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

### Application

Helical Anchoring

### General

Coating	Painted
Number of Helices	1
Torque Rating	6000 ft-lbs
Type	Anchor Helix
UPC	096359077367

### Dimensions

Anchor Helix Diameter(s)	10 in
Anchor Hub Size	1.375 in
Rod Diameter	<ul style="list-style-type: none"><li>• 0.750</li><li>• 1.000 in</li></ul>
Weight	12.711 lb

### Logistics

Pallet Quantity	144
Standard Package	4

### Product Assets

[Catalogs - Anchors \(4\)](#)  
[Installation Manuals - Holding Capacity Chart - Soil Classification](#)  
[Installation Manuals - TD06131E\\_PISA\\_Anchors](#)  
[Installation Manuals - Holding Capacity Chart - PISA Anchors \(TD06166E\)](#)  
[Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)  
[Literature - Anchoring \(CA12002E\)](#)  
[Literature - How to Match Anchors and Installing Wrenches \(O49114\)](#)  
[Sales Drawings - Helix And Core Assembly \(SA10200000\)](#)  
[Video - CHANCE Tough One and PISA Anchor Installation \(VI0645E\)](#)  
[Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

### Related Products

[C1021583 - Anchor, Tool, Drive End Wrench, Orange Band, rated 10,000 ft-lbs, 7ft long](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-E1021633-SPEC-EN | REV 7/2023