



## Ground Clamp, Flat Face, Type III-Class B-Grade 3, 1.5" Jaw Opening

By CHANCE Utility  
Catalog # [G33632](#)

Ground Clamp, Flat Face, Type III-Class B-Grade 3, 1.5" Jaw Opening



### Features

- Tower & Flat-Face Ground Clamp
- Continuous Current 400A
- Fault Current 27kA for 15 cycles or 20kA for 30 cycles
- Main Line Range Max. 1.5" Angles or 1.5" Flat
- Main Line Range Min. 1/8"
- Jumper Range Max. 2/0 Grd. Cable w/ Plain-Plug
- Jumper Range Min. #2 Grd. Cable w/ Plain-Plug
- ASTM Type III, Class B, Grade 3
- Jaws Serrated
- Ferrule Plain-Plug

### General

Eye Screw/T-Handle	N/A
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	N/A
Handle Type	T-Handle
Jaw Type	Serrated Jaws
Material	Bronze
Terminal Connection Type	Pressure
UPC	096359038146

### Dimensions

Jaw Opening Size - Maximum	1.5 in
Jaw Opening Size - Minimum	.125 in
Weight	2.94 lb

### Electrical Ratings

Current Rating	300 A
Fault Current - 15 Cycles	27000 A
Fault Current - 30 Cycles	20000 A
Grounding Wire Capacity Maximum	2/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

### Certifications and Compliance

Fault Current - ASTM Grade	ASTM Grade 3
----------------------------	--------------

### Logistics

Pallet Quantity	720
-----------------	-----

### Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-G33632-SPEC-EN | REV 7/2023