



CHANCE® Ground Clamp - C-Type, Type I-Class A-Grade 3, 0.998" Jaw Opening

By: CHANCE Lineman Tools & Equipment
Catalog # [G3403](#)

CHANCE® Ground Clamp - C-Type, Type I-Class A-Grade 3, 0.998" Jaw Opening



Features

- C-Type Ground Clamp Continuous Current 350A
- Fault Current 27kA for 15 cycles or 20kA for 30 cycles
- Main Line Range Max. 636 kcmil ACSR (0.998")
- Main Line Range Min. #8 Sol. CU (0.128in.)
- Jumper Range Max. 2/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 3
- Jaws Smooth
- Ferrule Plain-Plug

General

Eye Screw/T-Handle Installation Torque (in-lb)	250 in-lb
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	Pressure
UPC	096359038214

Dimensions

Jaw Opening Size - Maximum	.998 in
Jaw Opening Size - Minimum	.128 in
Weight	0.98 lb

Electrical Ratings

Current Rating	300 A
Fault Current - 15 Cycles	27000 A
Fault Current - 30 Cycles	20000 A
Grounding Wire Capacity Maximum	2/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

Certifications and Compliance

Fault Current - ASTM Grade	ASTM Grade 3
----------------------------	--------------

Product Assets

- [Catalogs - Grounding Equipment \(3000\)](#)
- [Sales Drawings - Ground Clamp \(SAG3403\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-G3403-SPEC-EN | REV 4/2023