



Duckbill Ground Clamp Cluster, Type I-Class A-Grade 4, 1.162" Jaw Opening

By CHANCE Utility
Catalog # [G3803](#)

Duckbill Ground Clamp Cluster, Type I-Class A-Grade 4, 1.162"
Jaw Opening



Features

- Duckbill Ground Clamp Cluster
- Continuous Current 400A
- Fault Current 34kA for 15 cycles or 25kA for 30 cycles
- Main Line Range Max. 566kcmil CU or 900kcmil ACSR (1.162")
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 4
- Jaws Smooth
- Ferrule Plain-Plug

General

EU RoHS Indicator	No
Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	Pressure
UPC	096359038283

Dimensions

Jaw Opening Size - Maximum	1.162 in
Jaw Opening Size - Minimum	.162 in
Weight	6.468 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

Certifications and Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

Logistics

Pallet Quantity	72
-----------------	----

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-G3803-SPEC-EN | REV 8/2023