



CHANCE® 15KV ORANGE RUBBER GLOVE JUMPER CLAMP PAIR

By: CHANCE Lineman Tools & Equipment
Catalog # [G4758](#)



CHANCE® 15KV ORANGE RUBBER GLOVE JUMPER CLAMP PAIR

Features

- Designed and tested per ASTM F2321
- Maximum use voltage of 15kV
- Conductor range of #6 - 795 ACSR
- Robust orange body made from durable polyethylene plastic
- Handle length of 5-5/8" below handguard
- Includes 2 jumper clamps
- Used for bypassing work areas when equipment is under repair, upgrading lines, and making temporary or emergency repairs

General

EU RoHS Indicator No
Style 1 Pair of Clamps

Dimensions

Weight 2.25 lb

Electrical Ratings

Amperage Rating	300
Voltage - Maximum	15 kV
Voltage Rating	15 kV

Conductor Related

Conductor Diameter (Main) - Maximum	0.72 in
-------------------------------------	---------

Logistics

Pallet Quantity	216
-----------------	-----

Product Assets

[Catalogs - Jumpers & Load Pickup Tools \(2300\)](#)

[Literature - CHANCE® Orange Jumper Clamps \(SF09231E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-G4758-SPEC-EN | REV 4/2023