



CHANCE® 25KV ORANGE RUBBER GLOVE JUMPER CLAMP PAIR

By CHANCE Utility
Catalog # [G4765](#)

CHANCE® 25KV ORANGE RUBBER GLOVE JUMPER CLAMP PAIR



Features

- Designed and tested per ASTM F2321
- Maximum use voltage of 25kV
- Conductor range of #6 - 795 ACSR
- Robust orange body made from durable polyethylene plastic
- Handle length of 7-1/2" below handguard
- Includes 2 jumper clamps
- Used for bypassing work areas when equipment is under repair, upgrading lines, and making temporary or emergency repairs

General

EU RoHS Indicator No
Style 1 Pair of Clamps

Dimensions

Weight 2.75 lb

Electrical Ratings

Amperage Rating 400
Voltage - Maximum 25 kV
Voltage Rating 25 kV

Conductor Related

Conductor Diameter (Main) - 0.88 in
Maximum

Product Assets

[Catalogs - Jumpers & Load Pickup Tools \(2300\)](#)
[Literature - CHANCE® Orange Jumper Clamps \(SF09231E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-G4765-SPEC-EN | REV 8/2023