



COMBINATION GUY-HOOK/POLE  
EYE ATTACHMENT, 12,500 lbs.  
STRENGTH, 5/8in UPPER & LOWER  
BOLT SIZE, 11/16in CLEVIS PIN  
HOLE

By Chance  
Catalog # [GEP5](#)



\*Representative Image

Cast ductile iron combination guy- hook/pole-eye attachment  
for deadending guy wire to poles. Industry slang is Ram’s Head.

Features

- Backside cleats offer additional support for wood pole installations
- 2-1/2" base width x 5" overall length
- Ductile iron per ASTM A-536
- Galvanized per ASTM A-153
- RUS Listed, v2, Pole Eye Plates

General

Catalog Number	GEP5
Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
UPC	096359036500

Dimensions

Diameter - Mounting Bolt - Maximum	0.63 in
Dimensions	5.875 in x 3.625 in x 3.250 in
Distance From Pole	N/A
Height	3.25 in
Length	5.875 in
Weight	1.83 lb
Width	3.625 in

Logistics

Carton Quantity	15
-----------------	----

Product Assets

- [Catalogs - Cast Iron Pole Line Hardware \(05A\)](#)
- [Catalogs - Communications Catalog](#)
- [Sales Drawings - Multiple Guy Attachments](#)
- [Specifications - GEP5](#)