



COMBINATION GUY-HOOK/POLE-EYE ATTACHMENT, 21,000 lbs. STRENGTH, 3/4in UPPER & 5/8in LOWER BOLT SIZE, 13/16in CLEVIS HOLE

By Chance

Catalog # [GEP5A34N](#)

Cast ductile iron combination guy- hook/pole-eye attachment for deadending guy wire to poles. Industry slang is Ram's Head.



*Representative Image

Features

- Smooth backside surface (less cleats) for non-wood pole installations
- 2-1/2" base width x 5" overall length
- Ductile iron per ASTM A-536
- Galvanized per ASTM A-153

General

Catalog Number	GEP5A34N
Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
UPC	096359389521

Dimensions

Diameter - Mounting Bolt - Maximum	0.75 in
Dimensions	6.000 in x 3.625 in x 3.250 in
Distance From Pole	N/A
Height	3.25 in
Length	6 in
Weight	1.69 lb
Width	3.625 in

Logistics

Carton Quantity	25
Pallet Quantity	1200

Product Assets

[Catalogs - Cast Iron Pole Line Hardware \(05A\)](#)

[Sales Drawings - Multiple Guy Attachment](#)