



COMBINATION GUY-HOOK/POLE-EYE ATTACHMENT, 16,000 lbs. STRENGTH, 3/4in UPPER & 5/8in LOWER BOLT SIZE, 11/16in CLEVIS HOLE

By Chance
Catalog # [GEP5AN](#)

Cast ductile iron combination guy- hook/pole-eye attachment for deadending guy wire to poles. Industry slang is Ram's Head.



*Representative Image

Features

- Smooth backside surface (less cleats) for non-wood pole installations
- 2-1/2" base width x 5" overall length
- Ductile iron per ASTM A-536
- Galvanized per ASTM A-153

General

Catalog Number	GEP5AN
Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
UPC	096359466833

Dimensions

Diameter - Mounting Bolt - Maximum	0.75 in
Dimensions	5.750 in x 3.625 in x 3.125 in
Distance From Pole	N/A
Height	3.125 in
Length	5.75 in
Weight	1.8 lb
Width	3.625 in

Logistics

Carton Quantity	25
Pallet Quantity	1200

Product Assets

- [Catalogs - Cast Iron Pole Line Hardware \(05A\)](#)
- [Sales Drawings - Multiple Guy Attachments](#)