



# POLE EYE PLATE GUY ATTACHMENT, 21,000lbs RATED STRENGTH, 13/16in CLEVIS PIN HOLE, MOUNTS with 3/4in BOLTS

By CHANCE Utility  
Catalog # [GEP6](#)

Cast ductile iron pole eye plate for attaching to fiberglass guy strains or clevis fittings is rated for 20,000 lbs. at 45 and 90 degrees. Has 13/16" clevis hole and 13/16" upper and lower mounting holes as well as two 9/16" lag holes in the wide base. Common industry slang is Monkey Face.



## Features

- Wide base for stabilization
- Spurs on back side resist down-slotting
- Cast ductile iron per ASTM A-536
- galvanized per ASTM A-153

## General

Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
UPC	096359036586

## Dimensions

Distance From Pole	N/A
Weight	2.73 lb

## Certifications and Compliance

RUS Listed Reference      Pole Eye Plates (5/8" Bolt)

## Logistics

Pallet Quantity      720

## Product Assets

- [Catalogs - Communications Catalog \(CA12042E\)](#)
- [Catalogs - Cast Iron Pole Line Hardware \(05A\)](#)
- [Sales Drawings - Pole Eye Plate \(SAGEP6\)](#)



A proud member of the Hubbell Family.