



POLE EYE PLATE GUY ATTACHMENT, 21,000lbs RATED STRENGTH, 13/16in CLEVIS PIN HOLE, MOUNTS with 3/4in BOLTS

By Chance
Catalog # [GEP6N](#)

Cast ductile iron pole eye plate for attaching to fiberglass guy strains or clevis fittings is rated for 21,000 lbs. at 45 and 90 degrees. Has 13/16" clevis hole and 13/16" upper and lower mounting holes as well as two 9/16" lag holes in the wide base. There are no cleats on back side, allowing for non-wood pole mounting. Common industry slang is Monkey Face.

Features

- Wide base for stabilization
- Cast ductile iron per ASTM A-536
- Galvanized per ASTM A-153

General

Catalog Number	GEP6N
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Ductile Iron, ASTM A-536
UPC	096359511359

Dimensions

Dimensions	6.750 in x 4.000 in x 3.250 in
Distance From Pole	N/A



*Representative Image

Height	3.25 in
Length	6.75 in
Weight	0.98 lb
Width	4 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	720
-----------------	-----

Product Assets

- [Catalogs - Cast Iron Pole Line Hardware \(05A\)](#)
- [Sales Drawings - Pole Eye Plate](#)
- [Specifications - GEP6N](#)



A Hubbell brand