



POLE EYE PLATE GUY ATTACHMENT, 42,000lbs RATED STRENGTH, 15/16in CLEVIS PIN HOLE, MOUNTS with 7/8in BOLTS

By CHANCE Utility
Catalog # [GEP7A](#)

Pole eye plate has 15/16" dia. pin hole for clevis attachment. Rated for 42,000 lbs. tensile strength at 45 or 90 degrees. Has 15/16" x 2" upper mounting slot and 15/16" x 1-1/4" lower slot for mounting bolts. Common industry slang is Monkey Face.

Features

- Wide base for stabilization
- Spurs on back side resist down-slotting
- Cast ductile iron per ASTM A-536
- galvanized per ASTM A-153

General

Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
UPC	096359036623



Dimensions

Distance From Pole	N/A
Weight	5.4 lb

Logistics

Pallet Quantity	192
-----------------	-----

Product Assets

[Catalogs - Cast Iron Pole Line Hardware \(05A\)](#)
[Sales Drawings - Pole Eye Plate \(SAGEP7A\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-GEP7A-SPEC-EN | REV 7/2023