



GUY-HOOK ATTACHMENT, 12,400 lbs. STRENGTH, 5/8in BOLT SIZE with 9/16in LOWER HOLE

By Chance
Catalog # GH5

Cast ductile iron guy-hook attachment for deadending guy or messenger wire. Industry slang is Ram’s Head.

Features

- Maximum strand size is 7/16"
- Backside surface cleats increase stability in wood pole installations
- 2-1/2" base width x 4-3/4" length
- Rating increases to 13,550 lbs. with ASTM A-307 thru-bolts
- Ductile Iron per ASTM A-536
- Galvanized per ASTM A-153
- Manufactured to specificaiton IEEE C135.90
- RUS listed, V - Guy Attachment

General

Catalog Number	GH5
Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
Tensile Strength	12400 lb.
UPC	096359036722

Dimensions



Dimensions	4.750 in x 3.600 in x 1.750 in
Distance From Pole	N/A
Height	1.75 in
Length	4.75 in
Weight	1.36 lb
Width	3.6 in

Certifications And Compliance

RUS Listed Reference	v - Guy Attachment
----------------------	--------------------

Logistics

Pallet Quantity	1200
-----------------	------

Product Assets

- [Catalogs - Cast Iron Pole Line Hardware \(05A\)](#)
- [Catalogs - Communications Catalog](#)
- [Sales Drawings - Guy Hook](#)
- [Specifications - GH5](#)



A Hubbell brand